# **NEW SYMPRO**

# Denture cleaning unit

Compact denture cleaning unit especially suitable for cleaning removable dental restorations, orthodontic appliances and splints.

#### Advantages

- Customer retention a prophylaxis service for denture
- Processing reliability validated, hygienic reprocessing of system components.
- Patient satisfaction externally tested material compatibility with standard dental materials.

#### **Details**

- Positive effect on the patient's overall health due to regular denture cleaning.
- High time savings compared to manual methods thanks to effective and automated cleaning process.
- Optimized pin geometry for gentle and at same time effective cleaning.
- High cleaning performance due to optimal bowl inclination.

#### Making work easy

Uncompromising cleaning with SYMPRO system. Effective cleaning agents are available for cleaning with the SYMPRO denture cleaning unit, see page 7.

Easy cleaning of temporary restorations in combination with SYMPRO mini cup and temp:ex temporary cement remover.





Denture before and after cleaning with SYMPRO and help:ex

#### **Technical Data**

Permissible mains voltage	100-240 V
Permissible mains frequency	50/60 Hz
Power consumption	90 VA
Cleaning intensity	low / medium / high
Noise level	< 70 dB(A)
Dimensions (W x H x D)	150 x 240 x 280 mm
Weight (without bowl)	~3 kg

### Ordering information

SYMPRO, 100-240 V	No. 67001000
help:ex Cleaning agents	Page 7
More accessories	Page 19

## **Authorised Distributor**













